

Flat suction cup (oval)

SAOF 80x40 HT2-65 G1/4-IG

Art.-Nr.: 10.01.05.00750




Technical data

Attribute	Value
Suction cup material	High temperature material HT2
Material hardness [Shore A]	65.0 Shore A
Dimension (LxW)	80 x 40
Connection	G1/4-IG
Nipple material	Nickel plated

SAOF 80x40 HT2-65 G1/4-IG

Suction cup SAOF HT2, available in various dimensions, is delivered with connection nipple glued to elastomer part.



Design data

Attribute	Value
Height H	28.00 mm
Nominal diameter dn	6.00 mm
Thread G1	G1/4"-F
Thread length LG1	8.0 mm
Key width SW1	17.0 mm
Spring stroke Z	4.0 mm
Suction cup width Bs	38.60 mm
Ls	80.60 mm
Lmax.(S)	85.00 mm
Bmax(S)	43.00 mm

Design data SAOF 80x40 HT2-65 G1/4-IG



WWW.SCHMALZ.COM/10.01.05.00750

Art.-Nr.: 10.01.05.00750

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT2
Material hardness [Shore A]	65.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	50.0 mm
Suction force (-600mbar)	140.00 N
Weight	51.5 g
Dimension (LxW)	80 x 40
Lateral force	108.0 N
Volume	11.700 cm ³
Temperature resistance	200.0 °C
Number of folds	0.0
Connection	G1/4" -F
Product family	SAOF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00750

