

Düz vantuz (oval)

SAOF 100x50 HT2-65 G1/4-IG



Art.-Nr.: 10.01.05.00754




Teknik veriler

Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65,0 Shore A
Boyutlar (LxW)	100 x 50
Bağlantı	G1/4-IG
Meme ucu malzemesi	Nikel kaplama

SAOF 100x50 HT2-65 G1/4-IG

Çeşitli boyutlarda mevcut olan SAOF HT2 vantuz, elastomer parçaya yapıştırılmış bağlantı nipelini birlikte teslim edilir.



Tasarım verileri

Yükseklik H	30,00 mm
Nominal çap dn	8,00 mm
Diş G1	G1/4"-F
Diş uzunluğu LG1	8,0 mm
Anahtar boyutu SW1	17,0 mm
Yay stroku Z	5,0 mm
Vantuz genişliği Bs	48,10 mm
Ls	101,10 mm
Lmaks.(S)	106,00 mm
Bmaks(S)	54,00 mm

Tasarım verileri SAOF 100x50 HT2-65 G1/4-IG



WWW.SCHMALZ.COM/10.01.05.00754

Düz vantuz (oval)

SAOF 100x50 HT2-65 G1/4-IG



Art.-Nr.: 10.01.05.00754



Teknik veriler

Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	75,0 mm
Emme kuvveti (-600mbar)	217,00 N
Ağırlık	91,60 g
Boyutlar (LxW)	100 x 50
Yanal kuvvet	177,0 N
Cilt	21,800 cm ³
Sıcaklık direnci	200,0 °C
Körük Sayısı	0,0
Bağlantı	G1/4"-F
Ürün ailesi	SAOF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



WWW.SCHMALZ.COM/10.01.05.00754