


**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65.0 Shore A
Boyutlar (LxW)	60 x 23
Bağlantı	G1/4-IG
Meme ucu malzemesi	Nikel kaplama

SAOF 60x23 HT2-65 G1/4-IG

Çeşitli boyutlarda mevcut olan SAOF HT2 vantuz, elastomer parçaya yapıştırılmış bağlantı nipel ile birlikte teslim edilir.

**Tasarım verileri**

Attribute	Value
Yükseklik H	26.00 mm
Nominal çap dn	6.00 mm
Dış G1	G1/4"-F
Dış uzunluğu LG1	8.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	3.0 mm
Vantuz genişliği Bs	21.60 mm
Ls	60.60 mm
Lmaks.(S)	64.00 mm
Bmax(S)	25.00 mm

Tasarım verileri SAOF 60x23 HT2-65 G1/4-IG

Düz vantuz (oval)

SAOF 60x23 HT2-65 G1/4-IG



Art.-Nr.: 10.01.05.00742



Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65.0 Shore A
Hortum çapı (tavsiye edilen) d	4.0 mm
İş parçası yarıçapı dak (dışbükey)	20.0 mm
Emme kuvveti (-600mbar)	57.00 N
Ağırlık	32.1 g
Boyutlar (LxW)	60 x 23
Yanal kuvvet	36.0 N
Cilt	3.890 cm ³
Sıcaklık direnci	200.0 °C
Körük Sayısı	0.0
Bağlantı	G1/4"-F
Ürün ailesi	SAOF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00742



WWW.SCHMALZ.COM/10.01.05.00742