

Flat suction cup (oval)

SAOF 90x30 HT2-65 G3/8-IG

Art.-Nr.: 10.01.05.00745




Technical data

Attribute	Value
Suction cup material	High temperature material HT2
Material hardness [Shore A]	65.0 Shore A
Dimension (LxW)	90 x 30
Connection	G3/8-IG
Nipple material	Nickel plated

SAOF 90x30 HT2-65 G3/8-IG

Suction cup SAOF HT2, available in various dimensions, is delivered with connection nipple glued to elastomer part.



Design data

Attribute	Value
Height H	27.00 mm
Nominal diameter dn	6.00 mm
Thread G1	G3/8"-F
Thread length LG1	9.0 mm
Key width SW1	22.0 mm
Spring stroke Z	3.0 mm
Suction cup width Bs	30.60 mm
Ls	90.60 mm
Lmax.(S)	94.00 mm
Bmax(S)	34.00 mm

Design data SAOF 90x30 HT2-65 G3/8-IG



WWW.SCHMALZ.COM/10.01.05.00745

Art.-Nr.: 10.01.05.00745

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT2
Material hardness [Shore A]	65.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	40.0 mm
Suction force (-600mbar)	122.00 N
Weight	68.6 g
Dimension (LxW)	90 x 30
Lateral force	94.0 N
Volume	7.000 cm ³
Temperature resistance	200.0 °C
Number of folds	0.0
Connection	G3/8"-F
Product family	SAOF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00745

