

Плоская присоска (овальная)

SGO 30x10 FPM-50 N022

Art.-Nr.: 10.01.05.00848



Технические данные

Attribute	Value
Материал присоски	Фторкаучук FPM
Твердость материала [Shore A]	50,0 Shore A
Размеры (ДxШ)	30x10

SGO 30x10 FPM-50 N022

Конструктивные данные

Attribute	Value
Высота H2	3,00 mm
Высота H	12,00 mm
Диаметр головки Dk	11,5 mm
Номинальный диаметр dn	2,50 mm
Внутренний диаметр d1	7,0 mm
Внутренний диаметр d	5,50 mm
Ход пружины Z	1,5 mm
Высота H3	5,50 mm
Ширина присоски Bs	9,40 mm
Ls	29,40 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Конструктивные данные SGO 30x10 FPM-50 N022



WWW.SCHMALZ.COM/10.01.05.00848

1

Плоская присоска (овальная)

SGO 30x10 FPM-50 N022



Art.-Nr.: 10.01.05.00848



Технические данные

Attribute	Value
Материал присоски	Фторкаучук FPM
Твердость материала [Shore A]	50,0 Shore A
Вес	1,8 g
Семейство продуктов	SGO
Размеры (ДxШ)	30x10

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00848



WWW.SCHMALZ.COM/10.01.05.00848