


SGO 15x5 NBR-ESD-55 N021

Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR-ESD
Твердость материала [Shore A]	55.0 Shore A



Конструктивные данные SGO 15x5 NBR-ESD-55 N021

Конструктивные данные

Attribute	Value
Высота H2	3.00 mm
Высота H	12.00 mm
Диаметр головки Dk	8.5 mm
Номинальный диаметр dn	1.20 mm
Внутренний диаметр d1	6.0 mm
Внутренний диаметр d	4.50 mm
Ход пружины Z	0.7 mm
Высота H3	5.50 mm
Ширина присоски Bs	4.60 mm
Ls	14.60 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Плоская присоска (овальная)

SGO 15x5 NBR-ESD-55 N021



Art.-Nr.: 10.01.05.00931



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR-ESD
Твердость материала [Shore A]	55.0 Shore A
Всасывающая сила (-600 мбар)	3.10 N
Вес	0.4 g
Семейство продуктов	SGO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00931



WWW.SCHMALZ.COM/10.01.05.00931