

Düz vantuz (oval)

SGO 30x10 FPM-50 N022

Art.-Nr.: 10.01.05.00848



SGO 30x10 FPM-50 N022

Teknik veriler

Attribute	Value
Vantuz malzemesi	Fluorocaotchuc FPM
Malzeme sertliği [Shore A]	50,0 Shore A
Boyutlar (LxW)	30x10

Tasarım verileri

Attribute	Value
Yükseklik H2	3,00 mm
Yükseklik H	12,00 mm
Kafa çapı Dk	11,5 mm
Nominal çap dn	2,50 mm
İç çap d1	7,0 mm
İç çap d	5,50 mm
Yay stroku Z	1,5 mm
Yükseklik H3	5,50 mm
Vantuz genişliği Bs	9,40 mm
Ls	29,40 mm
Lmaks.(S)	30,50 mm
Bmaks(S)	11,50 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri SGO 30x10 FPM-50 N022



WWW.SCHMALZ.COM/10.01.05.00848

1

Düz vantuz (oval)

SGO 30x10 FPM-50 N022



Art.-Nr.: 10.01.05.00848



Teknik veriler

Attribute	Value
Vantuz malzemesi	Fluorocaotchuc FPM
Malzeme sertliđi [Shore A]	50,0 Shore A
Ađırlık	1,80 g
Ürün ailesi	SGO
Boyutlar (LxW)	30x10

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00848



WWW.SCHMALZ.COM/10.01.05.00848