




Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR-ESD
Твердость материала [Shore A]	55,0 Shore A
Размеры (ДхШ)	7x3.5
Свойство материала	немаркий

SGO 7x3.5 NBR-ESD-55 N003



Конструктивные данные

Attribute	Value
Высота H2	1,50 mm
Высота H	6,00 mm
Диаметр головки Dk	6,0 mm
Номинальный диаметр dn	1,50 mm
Внутренний диаметр d	1,50 mm
Ход пружины Z	0,8 mm
Ширина присоски Bs	3,50 mm
Ls	7,00 mm
Lmax.(S)	7,50 mm
Bmax(S)	4,50 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Конструктивные данные SGO 7x3.5 NBR-ESD-55 N003

Плоская присоска (овальная)

SGO 7x3.5 NBR-ESD-55 N003



Art.-Nr.: 10.01.05.00929



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR-ESD
Твердость материала [Shore A]	55,0 Shore A
Всасывающая сила (-600 мбар)	1,00 N
Вес	0,2 g
Семейство продуктов	SGO
Размеры (ДхШ)	7x3.5

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00929



WWW.SCHMALZ.COM/10.01.05.00929