




SGO 4x2 NBR-ESD-55 N003

Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR-ESD
Твердость материала [Shore A]	55,0 Shore A
Размеры (ДхШ)	4x2



Конструктивные данные SGO 4x2 NBR-ESD-55 N003

Конструктивные данные

Attribute	Value
Высота H2	1,50 mm
Высота H	6,00 mm
Диаметр головки Dk	6,0 mm
Номинальный диаметр dn	1,20 mm
Внутренний диаметр d	1,50 mm
Ход пружины Z	0,5 mm
Ширина присоски Bs	2,00 mm
Ls	4,00 mm
Lmax.(S)	4,50 mm
Bmax(S)	2,50 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Плоская присоска (овальная)

SGO 4x2 NBR-ESD-55 N003



Art.-Nr.: 10.01.05.00937



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR-ESD
Твердость материала [Shore A]	55,0 Shore A
Всасывающая сила (-600 мбар)	0,40 N
Вес	0,1 g
Семейство продуктов	SGO
Размеры (ДхШ)	4x2

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00937



WWW.SCHMALZ.COM/10.01.05.00937