

Flat suction cup (oval)

## SGO 90x30 SI-HD-65 N023




Art.-Nr.: 10.01.05.01041



### Teknik veriler

Vantuz malzemesi	Silikon SI-HD
Malzeme sertliği [Shore A]	65,0 Shore A
Boyutlar (LxW)	90x30

SGO 90x30 SI-HD-65 N023



### Tasarım verileri

Yükseklik H2	8,00 mm
Yükseklik H	21,00 mm
Kafa çapı Dk	17,5 mm
Nominal çap dn	4,00 mm
İç çap d1	13,0 mm
İç çap d	11,50 mm
Yay stroku Z	3,5 mm
Yükseklik H3	10,00 mm
Vantuz genişliği Bs	29,00 mm
Ls	89,00 mm
Lmaks.(S)	92,50 mm
Bmax(S)	33,00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri SGO 90x30 SI-HD-65 N023



[WWW.SCHMALZ.COM/10.01.05.01041](http://WWW.SCHMALZ.COM/10.01.05.01041)

1

Flat suction cup (oval)

## SGO 90x30 SI-HD-65 N023



Art.-Nr.: 10.01.05.01041



### Teknik veriler

Vantuz malzemesi	Silikon SI-HD
Malzeme sertliđi [Shore A]	65,0 Shore A
Emme kuvveti (-600mbar)	112,60 N
Ađırlık	25,70 g
Ürün ailesi	SGO
Boyutlar (LxW)	90x30

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



### Sipariř Verisi Aksesuarlar 10.01.05.01041

Typ		Ürün numarası
Vantuz bađlantı nipelı	SA-NIP N023 G1/4-AG DN350	10.01.05.00122
Vantuz bađlantı nipelı	SA-NIP N023 G1/4-IG DN350	10.01.05.00121



[WWW.SCHMALZ.COM/10.01.05.01041](http://WWW.SCHMALZ.COM/10.01.05.01041)