

Düz vantuz (oval)

SGO 18x6 NBR-ESD-55 N021




Art.-Nr.: 10.01.05.00932



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyutlar (LxW)	18x6

SGO 18x6 NBR-ESD-55 N021



Tasarım verileri

Attribute	Value
Yükseklik H2	3,00 mm
Yükseklik H	12,00 mm
Kafa çapı Dk	8,5 mm
Nominal çap dn	1,50 mm
İç çap d1	6,0 mm
İç çap d	4,50 mm
Yay stroku Z	0,8 mm
Yükseklik H3	5,50 mm
Vantuz genişliği Bs	5,60 mm
Ls	17,60 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri SGO 18x6 NBR-ESD-55 N021



WWW.SCHMALZ.COM/10.01.05.00932

Düz vantuz (oval)

SGO 18x6 NBR-ESD-55 N021



Art.-Nr.: 10.01.05.00932



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Emme kuvveti (-600mbar)	4,50 N
Ağırlık	0,50 g
Ürün ailesi	SGO
Boyutlar (LxW)	18x6

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00932



WWW.SCHMALZ.COM/10.01.05.00932