




FG 7 NBR-55 N016

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	7.00
Number of folds	2.5



Design data FG 7 NBR-55 N016

Design data

Attribute	Value
Height H2	3.80 mm
Height H	14.00 mm
Outside diameter D1	6.5 mm
Head diameter Dk	9.0 mm
d2	1.8 mm
Internal diameter d	4.50 mm
Spring stroke Z	3.0 mm
Diameter Ds	5.9 mm
Height H3	6.50 mm
Diameter Dmax(S)	7.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Art.-Nr.: 10.01.06.00050

**Technical data**

Attribute	Value
Nipple family	N 016
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	7.5 mm
Pull-off force	0.90 N
Suction force (-600mbar)	0.15 N
Weight	0.5 g
Volume	0.162 cm ³
Size	7.00
Number of folds	2.5
Product family	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00050

**Ordering Data Accessories 10.01.06.00050**

Typ		Item number
Suction cup connection nipple	SA-NIP N016 G1/8-AG DN350	10.01.06.05735
Suction cup connection nipple	SA-NIP N016 G1/8-IG DN350	10.01.06.05731
Suction cup connection nipple	SA-NIP N016 M5-AG DN250	10.01.06.00123

