




FSGPL 200 NBR-55 G1/2-IG

Çeşitli çaplarda mevcut olan FSGPL vantuz, elastomer parçaya vulkanize edilmiş destek plakası ile birlikte teslim edilir.



Tasarım verileri FSGPL 200 NBR-55 G1/2-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	200.00
Körük Sayısı	1.5
Vakum bağlantısı	G1/2"-F
Meme ucu malzemesi	Çelik

Tasarım verileri

Attribute	Value
Yükseklik H	54.00 mm
Dış çap D1	202.0 mm
d2	137.0 mm
Dış G1	G1/2"-F
Dış uzunluğu LG1	8.0 mm
Delik boyutu d3	119.4 mm
Yay stroku Z	37.2 mm
Çap Ds	191.0 mm
Yükseklik H4	8.00 mm
Çap Dmax(S)	208.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00102

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	12.0 mm
İş parçası yarıçapı dak (dışbükey)	350.0 mm
Çekme kuvveti	950.00 N
Emme kuvveti (-600mbar)	850.00 N
Ağırlık	1017.0 g
Cilt	876.516 cm ³
Boyut	200.00
Körük Sayısı	1.5
Ürün ailesi	FSGPL

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00102

WWW.SCHMALZ.COM/10.01.06.00102