


Art.-Nr.: 10.01.06.00108



FGB 25 SI-55 N049

Технические данные

Attribute	Value
Материал присоски	Силикон SI
Твердость материала [Shore A]	55,0 Shore A
размер	25,00
Количество складок	3,5



Конструктивные данные FGB 25 SI-55 N049

Конструктивные данные

Attribute	Value
Высота H2	9,00 mm
Высота H	43,00 mm
Наружный диаметр D1	25,0 mm
Диаметр головки Dk	10,0 mm
d2	10,0 mm
Внутренний диаметр d	5,00 mm
Ход пружины Z	22,0 mm
Диаметр Ds	23,0 mm
Диаметр Dmax(S)	26,5 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3



Art.-Nr.: 10.01.06.00108



Технические данные

Attribute	Value
Материал присоски	Силикон SI
Радиус заготовки мин. (выпуклый)	25,0 mm
Сила отрыва	20,00 N
Всасывающая сила (-600 мбар)	4,50 N
Вес	5,5 g
Объем	7,071 cm ³
размер	25,00
Количество складок	3,5
Семейство продуктов	FGB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00108

