




FGA 53 SI-55 N018

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	53.00
Körük Sayısı	1.5
Malzeme özellikleri	FDA uyumlu



Tasarım verileri FGA 53 SI-55 N018

Tasarım verileri

Attribute	Value
Yükseklik H2	12.30 mm
Yükseklik H	34.00 mm
Dış çap D1	58.6 mm
Kafa çapı Dk	18.0 mm
İç çap d1	14.5 mm
d2	33.0 mm
İç çap d	8.00 mm
Yay stroku Z	15.0 mm
Çap Ds	50.0 mm
Yükseklik H3	19.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00128

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Silikon SI
İş parçası yarıçapı dak (dışbükey)	75.0 mm
Emme kuvveti (-600mbar)	51.30 N
Ağırlık	18.8 g
Boyut	53.00
Körük Sayısı	1.5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00128

**Sipariş Verisi Aksesuarlar 10.01.06.00128**

Typ	Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N018 G1/4-AG DN440
Vantuz bağlantı nipeli	SA-NIP N018 G1/4-IG DN440

