




FG 60 VU1-72 N014 ON

Technical data

Attribute	Value
Suction cup material	Vulkollan VU1
Material hardness [Shore A]	72.0 Shore A
Size	60.00
Number of folds	2.5



Design data FG 60 VU1-72 N014 ON

Design data

Attribute	Value
Height H2	12.00 mm
Height H	55.00 mm
Outside diameter D1	60.0 mm
Head diameter Dk	21.0 mm
Internal diameter d1	20.0 mm
d2	36.0 mm
Internal diameter d	12.00 mm
Spring stroke Z	30.0 mm
Diameter Ds	57.0 mm
Height H3	17.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Art.-Nr.: 10.01.06.00208

**Technical data**

Attribute	Value
Nipple family	N 014
Suction cup material	Vulkollan VU1
Material hardness [Shore A]	72.0 Shore A
Workpiece radius min. (convex)	40.0 mm
Pull-off force	100.00 N
Suction force (-600mbar)	61.00 N
Weight	38.8 g
Volume	66.755 cm ³
Size	60.00
Number of folds	2.5
Product family	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00208

**Ordering Data Accessories 10.01.06.00208**

Typ		Item number
Suction cup connection nipple	SA-NIP N014 G1/4-AG DN600	10.01.06.00184
Suction cup connection nipple	SA-NIP N014 G1/4-IG DN600	10.01.06.00181

