



FGA 40 VU1-72 N011 ON


Technical data

Attribute	Value
Suction cup material	Vulkollan VU1
Material hardness [Shore A]	72.0 Shore A
Size	40.00
Number of folds	1.5

Design data

Attribute	Value
Height H2	8.00 mm
Height H	27.00 mm
Outside diameter D1	40.0 mm
Head diameter Dk	14.0 mm
Internal diameter d1	13.6 mm
d2	26.8 mm
Internal diameter d	8.00 mm
Spring stroke Z	12.8 mm
Diameter Ds	38.0 mm
Height H3	15.00 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



Design data FGA 40 VU1-72 N011 ON

Art.-Nr.: 10.01.06.00301

**Technical data**

Attribute	Value
Suction cup material	Vulkollan VU1
Workpiece radius min. (convex)	40.0 mm
Pull-off force	56.00 N
Suction force (-600mbar)	33.00 N
Weight	9.0 g
Volume	12.888 cm ³
Size	40.00
Number of folds	1.5
Product family	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00301

**Ordering Data Accessories 10.01.06.00301**

Typ		Item number
Suction cup connection nipple	SA-NIP N011 G1/4-AG DN350	10.01.01.10663
Suction cup connection nipple	SA-NIP N011 G1/4-IG DN350	10.01.01.00412

