

Art.-Nr.: 10.01.06.00381

**Technical data**


Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	14.00
Number of folds	1.5
Connection	G1/8"-M
Vacuum connection	G1/8"-M
Nipple material	Aluminum

FSGA 14 NBR-55 G1/8-AG

Suction cup FSGA (elastomer part + connection nipple) is delivered unassembled (diameters of 33 mm and more are assembled). The delivery consists of:

- Suction cup of type FGA – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup FGA, connection nipple SA-NIP

**Design data**

Height H	21.50 mm
Nominal diameter dn	3.50 mm
d2	5.0 mm
Thread G1	G1/8"-M
Thread length LG1	7.5 mm
Key width SW1	14.0 mm
Spring stroke Z	5.0 mm
Diameter Ds	12.5 mm
Diameter Dmax(S)	14.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FSGA 14 NBR-55 G1/8-AG



Art.-Nr.: 10.01.06.00381

**Technical data**

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	15.0 mm
Pull-off force	5.00 N
Suction force (-600mbar)	1.20 N
Weight	4.80 g
Volume	0.420 cm <sup>3</sup>
Size	14.00
Number of folds	1.5
Product family	FSGA
Connection	G1/8-AG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.06.00381**

Typ	Item number
Schmalz Pad Insert PEEK   SPI 14 PEEK	10.01.06.03282

**Ordering Data Spare Parts 10.01.06.00381**

Typ	Item number
Suction cup connection nipple   SA-NIP N016 G1/8-AG DN350	10.01.06.05735

**Ordering Data Wear Parts 10.01.06.00381**

Typ	Item number
Bellows suction cup (round)   FGA 14 NBR-55 N016	10.01.06.00370

