




FGA 53 NK-45 N018

Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	53,00
Körük Sayısı	1,5



Tasarım verileri FGA 53 NK-45 N018

Tasarım verileri

Attribute	Value
Yükseklik H2	12,30 mm
Yükseklik H	34,00 mm
Dış çap D1	58,6 mm
Kafa çapı Dk	18,0 mm
İç çap d1	14,5 mm
d2	33,0 mm
İç çap d	8,00 mm
Yay stroku Z	15,0 mm
Çap Ds	50,0 mm
Yükseklik H3	19,00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00428

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
İş parçası yarıçapı dak (dışbükey)	75,0 mm
Emme kuvveti (-600mbar)	51,30 N
Ağırlık	16,90 g
Boyut	53,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00428

**Sipariş Verisi Aksesuarlar 10.01.06.00428**

Typ	Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N018 G1/4-AG DN440
Vantuz bağlantı nipeli	SA-NIP N018 G1/4-IG DN440

WWW.SCHMALZ.COM/10.01.06.00428