

Körüklü vantuz (yuvarlak)


FGA 33 NK-45 N018



Art.-Nr.: 10.01.06.00426



FGA 33 NK-45 N018



Tasarım verileri FGA 33 NK-45 N018

Teknik veriler

Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	33,00
Körük Sayısı	1,5

Tasarım verileri

Yükseklik H2	13,00 mm
Yükseklik H	27,00 mm
Dış çap D1	36,0 mm
Kafa çapı Dk	18,0 mm
İç çap d1	16,0 mm
d2	17,0 mm
İç çap d	8,00 mm
Yay stroku Z	9,0 mm
Çap Ds	30,0 mm
Yükseklik H3	14,00 mm
Çap Dmax(S)	38,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.06.00426

Körüklü vantuz (yuvarlak)

FGA 33 NK-45 N018



Art.-Nr.: 10.01.06.00426



Teknik veriler

Vantuz malzemesi	Doğal Kauçuk NK
İş parçası yarıçapı dak (dışbükey)	40,0 mm
Ağırlık	7,00 g
Boyut	33,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Sipariş Verisi Aksesuarlar 10.01.06.00426

Typ		Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N018 G1/4-AG DN440	10.01.06.01065
Vantuz bağlantı nipeli	SA-NIP N018 G1/4-IG DN440	10.01.06.01066
Schmalz Ped Ek Parçası PEEK	SPI 32 PEEK	10.01.06.03287



WWW.SCHMALZ.COM/10.01.06.00426