




FGAO 140x65 VU1-72 N039

Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
Boyutlar (LxW)	140 x 65
Körük Sayısı	1.5



Tasarım verileri FGAO 140x65 VU1-72 N039

Tasarım verileri

Attribute	Value
Uzunluk L1	140.00 mm
Genişlik B1	65.00 mm
Yükseklik H	30.00 mm
İç çap d1	9.5 mm
İç çap d	15.50 mm
Yay stroku Z	16.0 mm
Delik aralığı X1	75.0 mm
Vantuz genişliği Bs	65.00 mm
Ls	140.00 mm
Lmaks.(S)	142.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Körüklü vantuz (oval)

FGAO 140x65 VU1-72 N039



Art.-Nr.: 10.01.06.00468



Teknik veriler

Attribute	Value
Vantuz malzemesi	Vulkollan VU1
Malzeme sertliği [Shore A]	72.0 Shore A
İş parçası yarıçapı dak (dışbükey)	30.0 mm
Çekme kuvveti	255.00 N
Emme kuvveti (-600mbar)	225.00 N
Ağırlık	71.5 g
Boyutlar (LxW)	140 x 65
Körük Sayısı	1.5
Ürün ailesi	FGAO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00468



WWW.SCHMALZ.COM/10.01.06.00468