




Технические данные

Attribute	Value
Материал присоски	Вулколан VU1
Твердость материала [Shore A]	72,0 Shore A
Размеры (ДхШ)	140 x 65
Количество складок	1,5

FGAO 140x65 VU1-72 N039



Конструктивные данные

Attribute	Value
Длина L1	140,00 mm
Ширина B1	65,00 mm
Высота H	30,00 mm
Внутренний диаметр d1	9,5 mm
Внутренний диаметр d	15,50 mm
Ход пружины Z	16,0 mm
Форма отверстия X1	75,0 mm
Ширина присоски Bs	65,00 mm
Ls	140,00 mm
Lмакс.(S)	142,00 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Конструктивные данные FGAO 140x65 VU1-72 N039



Art.-Nr.: 10.01.06.00468



Технические данные

Attribute	Value
Материал присоски	Вулколан VU1
Твердость материала [Shore A]	72,0 Shore A
Радиус заготовки мин. (выпуклый)	30,0 mm
Сила отрыва	255,00 N
Всасывающая сила (-600 мбар)	225,00 N
Вес	71,5 g
Размеры (ДхШ)	140 x 65
Количество складок	1,5
Семейство продуктов	FGAO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00468

