

Bellows suction cup (round)

## FG 52 SI-55 N018




Art.-Nr.: 10.01.06.00585



### Technical data

Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	52.00
Number of folds	2.5
Material characteristics	FDA-compatible

FG 52 SI-55 N018



### Design data

Height H2	13.00 mm
Height H	48.70 mm
Outside diameter D1	52.0 mm
Head diameter Dk	18.0 mm
d2	24.6 mm
Internal diameter d	8.00 mm
Spring stroke Z	25.0 mm
Diameter Ds	52.5 mm
Diameter Dmax(S)	55.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FG 52 SI-55 N018



[WWW.SCHMALZ.COM/10.01.06.00585](http://WWW.SCHMALZ.COM/10.01.06.00585)

1

Art.-Nr.: 10.01.06.00585

**Technical data**

Nipple family	N 018
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	75.0 mm
Pull-off force	96.00 N
Suction force (-600mbar)	28.52 N
Weight	22.90 g
Volume	37.587 cm <sup>3</sup>
Size	52.00
Number of folds	2.5
Product family	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.06.00585**

Typ		Item number
Suction cup connection nipple	SA-NIP N018 G1/4-AG DN440	10.01.06.01065
Suction cup connection nipple	SA-NIP N018 G1/4-IG DN440	10.01.06.01066

