




Технические данные

Attribute	Value
Материал присоски	Вулкан VU1
Твердость материала [Shore A]	72,0 Shore A
Размеры (ДxШ)	95 x 40
Количество складок	1,5

FGAO 95x40 VU1-72 N038



Конструктивные данные

Attribute	Value
Длина L1	93,00 mm
Ширина B1	38,00 mm
Высота H	23,50 mm
Внутренний диаметр d1	7,5 mm
Внутренний диаметр d	11,50 mm
Ход пружины Z	12,0 mm
Форма отверстия X1	55,0 mm
Ширина присоски Bs	40,00 mm
Ls	95,00 mm
Lmax(S)	97,00 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Конструктивные данные FGAO 95x40 VU1-72 N038

Art.-Nr.: 10.01.06.00499



Технические данные

Attribute	Value
Материал присоски	Вулколан VU1
Твердость материала [Shore A]	72,0 Shore A
Радиус заготовки мин. (выпуклый)	20,0 mm
Сила отрыва	110,00 N
Всасывающая сила (-600 мбар)	95,00 N
Вес	20,9 g
Размеры (ДхШ)	95 x 40
Количество складок	1,5
Семейство продуктов	FGAO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00499



WWW.SCHMALZ.COM/10.01.06.00499