




FGA 110 NBR-55 N010

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	110,00
Körük Sayısı	1,5



Tasarım verileri FGA 110 NBR-55 N010

Tasarım verileri

Attribute	Value
Yükseklik H	55,00 mm
Dış çap D1	123,0 mm
Kafa çapı Dk	86,0 mm
d2	80,0 mm
İç çap d	7,00 mm
Dmk	40,0 mm
Yay stroku Z	29,0 mm
Çap Ds	111,0 mm
Yükseklik H4	8,00 mm
Çap Dmax(S)	130,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Körüklü vantuz (yuvarlak)

FGA 110 NBR-55 N010



Art.-Nr.: 10.01.06.00629



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	110,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00629



Sipariş Verisi Aksesuarlar 10.01.06.00629

Typ	Ürün numarası
Vantuz bağlantı nipel (inst)	SA-NIP N010 G1/2-IG
	10.01.01.00796



WWW.SCHMALZ.COM/10.01.06.00629