

Bellows suction cup (round)

## FG 5 NBR-CO-55 N017




Art.-Nr.: 10.01.06.00641



### Technical data

Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55.0 Shore A
Size	5.00
Number of folds	2.5

FG 5 NBR-CO-55 N017



### Design data

Height H2	8.00 mm
Height H	14.00 mm
Outside diameter D1	6.0 mm
Head diameter Dk	7.0 mm
d2	2.6 mm
Internal diameter d	3.50 mm
Spring stroke Z	2.0 mm
Diameter Ds	5.0 mm
Diameter Dmax(S)	6.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FG 5 NBR-CO-55 N017



[WWW.SCHMALZ.COM/10.01.06.00641](http://WWW.SCHMALZ.COM/10.01.06.00641)

1

Bellows suction cup (round)

## FG 5 NBR-CO-55 N017



Art.-Nr.: 10.01.06.00641



### Technical data

Nipple family	N 017
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	2.0 mm
Pull-off force	0.80 N
Suction force (-600mbar)	0.32 N
Weight	0.30 g
Volume	1.369 cm <sup>3</sup>
Size	5.00
Number of folds	2.5
Product family	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



[WWW.SCHMALZ.COM/10.01.06.00641](http://WWW.SCHMALZ.COM/10.01.06.00641)