

Bellows suction cup (round)

FG 7 SI-CO-55 N016



Art.-Nr.: 10.01.06.00508



FG 7 SI-CO-55 N016

Technical data

Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55.0 Shore A
Size	7.00
Number of folds	2.5

Design data

Height H2	3.80 mm
Height H	14.00 mm
Outside diameter D1	6.5 mm
Head diameter Dk	9.0 mm
d2	1.8 mm
Internal diameter d	4.50 mm
Spring stroke Z	3.0 mm
Diameter Ds	5.9 mm
Height H3	6.50 mm
Diameter Dmax(S)	7.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FG 7 SI-CO-55 N016



WWW.SCHMALZ.COM/10.01.06.00508

Bellows suction cup (round)

FG 7 SI-CO-55 N016



Art.-Nr.: 10.01.06.00508



Technical data

Nipple family	N 016
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	7.5 mm
Pull-off force	0.90 N
Suction force (-600mbar)	0.15 N
Weight	0.50 g
Volume	0.162 cm ³
Size	7.00
Number of folds	2.5
Product family	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



WWW.SCHMALZ.COM/10.01.06.00508