

Bellows suction cup (round)

## FGA 11 SI-CO-55 N016



Art.-Nr.: 10.01.06.00509



FGA 11 SI-CO-55 N016

### Teknik veriler

Vantuz malzemesi	Silikon SI iletken
Malzeme sertliđi [Shore A]	55,0 Shore A
Boyut	11,00
Körük Sayısı	1,5

Tasarım verileri FGA 11 SI-CO-55 N016

### Tasarım verileri

Yükseklik H2	3,80 mm
Yükseklik H	16,00 mm
Dış çap D1	12,0 mm
Kafa çapı Dk	10,0 mm
d2	5,0 mm
İç çap d	4,50 mm
Yay stroku Z	4,0 mm
Çap Ds	10,4 mm
Yükseklik H3	9,30 mm
Çap Dmax(S)	13,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



[WWW.SCHMALZ.COM/10.01.06.00509](http://WWW.SCHMALZ.COM/10.01.06.00509)

Bellows suction cup (round)

## FGA 11 SI-CO-55 N016



Art.-Nr.: 10.01.06.00509



### Teknik veriler

Vantuz malzemesi	Silikon SI iletken
Emme kuvveti (-600mbar)	1,20 N
Boyut	11,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



[WWW.SCHMALZ.COM/10.01.06.00509](http://WWW.SCHMALZ.COM/10.01.06.00509)

2