




SAB 80 NBR-60 G1/4-AG

Suction cup SAB, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.



Design data SAB 80 NBR-60 G1/4-AG

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Size	80.00
Number of folds	1.5
Connection	G1/4-AG
Nipple material	Aluminum

Design data

Attribute	Value
Height H	49.90 mm
Outside diameter D1	63.6 mm
Nominal diameter dn	6.00 mm
Thread G1	G1/4"-M
Thread length LG1	10.0 mm
Key width SW1	22.0 mm
Spring stroke Z	22.1 mm
Diameter Ds	81.1 mm
Diameter Dmax(S)	89.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Art.-Nr.: 10.01.06.00806

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	75.0 mm
Pull-off force	221.00 N
Suction force (-600mbar)	135.00 N
Weight	72.10 g
Lateral force	205.0 N
Lateral force oily surface	140.0 N
Volume	67.600 cm ³
Size	80.00
Number of folds	1.5
Product family	SAB

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00806

