




FGA 63 SI-55 N018

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	63,00
Körük Sayısı	1,5
Malzeme özellikleri	FDA uyumlu



Tasarım verileri FGA 63 SI-55 N018

Tasarım verileri

Attribute	Value
Yükseklik H2	13,00 mm
Yükseklik H	34,00 mm
Dış çap D1	67,0 mm
Kafa çapı Dk	18,0 mm
İç çap d1	14,5 mm
d2	44,5 mm
İç çap d	8,00 mm
Yay stroku Z	15,0 mm
Çap Ds	60,0 mm
Yükseklik H3	18,80 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00689

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Silikon SI
İş parçası yarıçapı dak (dışbükey)	75,0 mm
Emme kuvveti (-600mbar)	85,00 N
Ağırlık	23,80 g
Boyut	63,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00689

**Sipariş Verisi Aksesuarlar 10.01.06.00689**

Typ	Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N018 G1/4-AG DN440
Vantuz bağlantı nipeli	SA-NIP N018 G1/4-IG DN440

WWW.SCHMALZ.COM/10.01.06.00689