




FGA 53 HT1-60 N018

Teknik veriler

Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	53,00
Körük Sayısı	1,5



Tasarım verileri FGA 53 HT1-60 N018

Tasarım verileri

Yükseklik H2	12,30 mm
Yükseklik H	34,00 mm
Dış çap D1	58,6 mm
Kafa çapı Dk	18,0 mm
İç çap d1	14,5 mm
d2	33,0 mm
İç çap d	8,00 mm
Yay stroku Z	15,0 mm
Çap Ds	50,0 mm
Yükseklik H3	19,00 mm
Çap Dmax(S)	60,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Körüklü vantuz (yuvarlak)

FGA 53 HT1-60 N018



Art.-Nr.: 10.01.06.00875



Teknik veriler

Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
İş parçası yarıçapı dak (dışbükey)	75,0 mm
Emme kuvveti (-600mbar)	51,30 N
Ağırlık	18,30 g
Boyut	53,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Sipariş Verisi Aksesuarlar 10.01.06.00875

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N018 G1/4-AG DN440
Vantuz bağlantı nipel	SA-NIP N018 G1/4-IG DN440



WWW.SCHMALZ.COM/10.01.06.00875