




FG 9 HT1-60 N016

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	9,00
Körük Sayısı	2,5



Tasarım verileri FG 9 HT1-60 N016

Tasarım verileri

Attribute	Value
Yükseklik H2	3,80 mm
Yükseklik H	15,00 mm
Dış çap D1	8,9 mm
Kafa çapı Dk	9,0 mm
d2	4,1 mm
İç çap d	4,50 mm
Yay stroku Z	3,0 mm
Çap Ds	9,0 mm
Yükseklik H3	8,20 mm
Çap Dmax(S)	9,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.00878

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 016
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
İş parçası yarıçapı dak (dışbükey)	10,0 mm
Çekme kuvveti	2,30 N
Emme kuvveti (-600mbar)	0,79 N
Ağırlık	0,60 g
Boyut	9,00
Körük Sayısı	2,5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00878

**Sipariş Verisi Aksesuarlar 10.01.06.00878**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N016 G1/8-AG DN350
Vantuz bağlantı nipel	SA-NIP N016 G1/8-IG DN350
Vantuz bağlantı nipel	SA-NIP N016 M5-AG DN250
Schmalz Ped Ek Parçası PEEK	SPI 9 PEEK

