

Bellows suction cup (round)

FGA 14 HT1-60 N016




Art.-Nr.: 10.01.06.00868



Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	14.00
Number of folds	1.5

FGA 14 HT1-60 N016



Design data

Height H2	3.80 mm
Height H	15.50 mm
Outside diameter D1	13.7 mm
Head diameter Dk	10.0 mm
d2	5.0 mm
Internal diameter d	4.50 mm
Spring stroke Z	4.0 mm
Diameter Ds	12.5 mm
Height H3	8.50 mm
Diameter Dmax(S)	14.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FGA 14 HT1-60 N016



WWW.SCHMALZ.COM/10.01.06.00868

Art.-Nr.: 10.01.06.00868

**Technical data**

Suction cup material	High temperature material HT1
Workpiece radius min. (convex)	12.5 mm
Suction force (-600mbar)	1.20 N
Weight	1.10 g
Size	14.00
Number of folds	1.5
Product family	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.06.00868**

Typ		Item number
Suction cup connection nipple	SA-NIP N016 G1/8-AG DN350	10.01.06.05735
Suction cup connection nipple	SA-NIP N016 G1/8-IG DN350	10.01.06.05731
Suction cup connection nipple	SA-NIP N016 M5-AG DN250	10.01.06.00123
Schmalz Pad Insert PEEK	SPI 14 PEEK	10.01.06.03282

