




FG 14 SI-55 N016 SO

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	14,00
Körük Sayısı	2,5
Malzeme özellikleri	FDA uyumlu



Tasarım verileri FG 14 SI-55 N016 SO

Tasarım verileri

Attribute	Value
Yükseklik H2	9,30 mm
Yükseklik H	18,50 mm
Dış çap D1	13,7 mm
Kafa çapı Dk	10,0 mm
d2	8,7 mm
İç çap d	5,00 mm
Yay stroku Z	4,0 mm
Çap Ds	13,7 mm
Yükseklik H3	9,30 mm
Çap Dmax(S)	14,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.01063

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 016
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
Çekme kuvveti	5,00 N
Emme kuvveti (-600mbar)	3,57 N
Cilt	0,869 cm ³
Boyut	14,00
Körük Sayısı	2,5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01063

**Sipariş Verisi Aksesuarlar 10.01.06.01063**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N016 G1/8-AG DN350
Vantuz bağlantı nipel	SA-NIP N016 G1/8-IG DN350
Vantuz bağlantı nipel	SA-NIP N016 M5-AG DN250
Vantuz bağlantı nipel	SA-NIP N016 M5-IG DN250

