


Bellows suction cup (rect.)

FGB-R 52x25 NBR-50


Art.-Nr.: 10.01.06.01115



FGB-R 52x25 NBR-50

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	50.0 Shore A
Dimension (LxW)	52 x 25
Number of folds	2.5



Design data

Attribute	Value
Length L1	52.00 mm
Width B1	25.00 mm
Height H	26.00 mm
Spring stroke Z	15.0 mm
Length L3	40.00 mm
Width B3	13.00 mm
Suction cup width Bs	25.00 mm
Ls	52.00 mm
Lmax.(S)	54.50 mm
Bmax(S)	27.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3 The specified stroke is for use with a supporting frame in each fold

Design data FGB-R 52x25 NBR-50



WWW.SCHMALZ.COM/10.01.06.01115

Art.-Nr.: 10.01.06.01115

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	50.0 Shore A
Workpiece radius min. (convex)	10.0 mm
Suction force (-600mbar)	20.00 N
Weight	8.0 g
Dimension (LxW)	52 x 25
Volume	16.000 cm ³
Number of folds	2.5
Product family	FGB-R

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01115

