

Bellows suction cup (round)

## SAB 30 NBR-60 RA



Art.-Nr.: 10.01.06.01203




### Technical data

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Size	30.00
Number of folds	1.5
Connection	RA
Nipple material	Aluminum

SAB 30 NBR-60 RA

Suction cup SAB, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.



### Design data

Height H	31.20 mm
Outside diameter D1	32.0 mm
Nominal diameter dn	4.00 mm
Spring stroke Z	9.0 mm
Diameter Ds	30.6 mm
Length L4	31.80 mm
Diameter Dmax(S)	34.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SAB 30 NBR-60 RA



[WWW.SCHMALZ.COM/10.01.06.01203](http://WWW.SCHMALZ.COM/10.01.06.01203)

Art.-Nr.: 10.01.06.01203

**Technical data**

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	40.0 mm
Pull-off force	33.00 N
Suction force (-600mbar)	22.00 N
Weight	26.90 g
Lateral force	30.0 N
Lateral force oily surface	13.0 N
Volume	5.600 cm <sup>3</sup>
Size	30.00
Number of folds	1.5
Product family	SAB

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

