




FG 5 HT1-60 N017

Teknik veriler

Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	5,00
Körük Sayısı	2,5



Tasarım verileri FG 5 HT1-60 N017

Tasarım verileri

Yükseklik H2	8,00 mm
Yükseklik H	14,00 mm
Dış çap D1	6,0 mm
Kafa çapı Dk	7,0 mm
d2	2,6 mm
İç çap d	3,50 mm
Yay stroku Z	2,0 mm
Çap Ds	5,0 mm
Çap Dmax(S)	6,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Körüklü vantuz (yuvarlak)

FG 5 HT1-60 N017



Art.-Nr.: 10.01.06.01250



Teknik veriler

Meme ucu ailesi	N 017
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
İş parçası yarıçapı dak (dışbükey)	2,0 mm
Emme kuvveti (-600mbar)	0,32 N
Ağırlık	0,30 g
Boyut	5,00
Körük Sayısı	2,5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Sipariş Verisi Aksesuarlar 10.01.06.01250

Typ		Ürün numarası
Vantuz bağlantı nipel	SA-NIP N017 M5-AG DN200	10.01.06.00314
Vantuz bağlantı nipel	SA-NIP N017 M5-IG DN200	10.01.06.00313
Schmalz Ped Ek Parçası PEEK	SPI 6 PEEK	10.01.06.03279



WWW.SCHMALZ.COM/10.01.06.01250