


FGB-R 52x25 SI-50

Технические данные

Attribute	Value
Материал присоски	Силикон SI
Твердость материала [Shore A]	50,0 Shore A
Размеры (ДхШ)	52 x 25
Количество складок	2,5



Конструктивные данные FGB-R 52x25 SI-50

Конструктивные данные

Attribute	Value
Длина L1	52,00 mm
Ширина B1	25,00 mm
Высота H	26,00 mm
Ход пружины Z	15,0 mm
Длина L3	40,00 mm
Ширина B3	13,00 mm
Ширина присоски Bs	25,00 mm
Ls	52,00 mm
Lмакс.(S)	54,50 mm
Vmax(S)	27,50 mm

Примечание: Допустимые отклонения на размеры резиновых деталей в соответствии с DIN ISO 3302-1 M3. Указанный ход относится к использованию с поддерживающей рамкой в каждой гофре

Art.-Nr.: 10.01.06.01116



Технические данные

Attribute	Value
Материал присоски	Силикон SI
Твердость материала [Shore A]	50,0 Shore A
Радиус заготовки мин. (выпуклый)	10,0 mm
Всасывающая сила (-600 мбар)	20,00 N
Вес	8,0 g
Размеры (ДхШ)	52 x 25
Объем	16,000 cm ³
Количество складок	2,5
Семейство продуктов	FGB-R

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01116



WWW.SCHMALZ.COM/10.01.06.01116