




SAB 30 NBR-60 M10-AG

Suction cup SAB, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Size	30.00
Number of folds	1.5
Connection	M10-AG
Nipple material	Steel



Design data SAB 30 NBR-60 M10-AG

Design data

Attribute	Value
Height H	28.00 mm
Outside diameter D1	32.0 mm
Nominal diameter dn	4.00 mm
Thread G1	M10-M
Thread length LG1	12.0 mm
Key width SW1	17.0 mm
Spring stroke Z	9.0 mm
Diameter Ds	30.6 mm
Diameter Dmax(S)	34.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Art.-Nr.: 10.01.06.01200

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	40.0 mm
Pull-off force	33.00 N
Suction force (-600mbar)	22.00 N
Weight	26.6 g
Lateral force	30.0 N
Lateral force oily surface	13.0 N
Volume	5.600 cm ³
Size	30.00
Number of folds	1.5
Product family	SAB

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01200

