


Art.-Nr.: 10.01.06.01679



DR 28/21x3 C03 EPDM-15 KE

Technical data

Attribute	Value
Material hardness [Shore A]	15.0 Shore A
Sealing material	EPDM
Additional function area gripper	Adhesive tape on one side
Height H	3.00 mm
Outside diameter D	28.00 mm
Internal diameter d	21.00 mm



Design data DR 28/21x3 C03 EPDM-15 KE

Design data

Attribute	Value
Length L	3.00 mm
Height H	3.00 mm
Outside diameter D	28.00 mm
Internal diameter d	21.00 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

**Technical data**

Attribute	Value
Weight	0.13 g

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Sealing ring

DR 28/21x3 C03 EPDM-15 KE



Art.-Nr.: 10.01.06.01679



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01679



WWW.SCHMALZ.COM/10.01.06.01679