


Technical data

Attribute	Value
Suction cup material	Polyvinyl chloride PVC
Material hardness [Shore A]	50.0 Shore A
Size	19.00
Number of folds	1.5

FGA 19 PVC-50 N056

Suction cup FGA PVC (elastomer part + connection element) is delivered assembled. The assembly consists of:

- Suction cup of type FGA PVC – elastomer part, available in various diameters
- Connection nipple of type SA-NIP – available with various threads



Design data

Attribute	Value
Height H2	8.20 mm
Height H	18.70 mm
Outside diameter D1	19.0 mm
Head diameter Dk	13.0 mm
d2	12.2 mm
Internal diameter d	6.60 mm
Spring stroke Z	6.0 mm
Diameter Ds	19.0 mm
Diameter Dmax(S)	21.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FGA 19 PVC-50 N056

Art.-Nr.: 10.01.06.01975

**Technical data**

Attribute	Value
Nipple family	N 056
Suction cup material	Polyvinyl chloride PVC
Material hardness [Shore A]	50.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	20.0 mm
Pull-off force	10.00 N
Suction force (-600mbar)	5.90 N
Weight	1.5 g
Volume	2.024 cm ³
Size	19.00
Number of folds	1.5
Product family	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.01975

**Ordering Data Accessories 10.01.06.01975**

Typ		Item number
Suction cup connection nipple	SA-NIP N056 M5-AG DN200	10.01.06.03080
Suction cup connection nipple	SA-NIP N056 G1/8-AG DN400	10.01.06.03571
Suction cup connection nipple	SA-NIP N056 G1/8-IG DN400	10.01.06.03572

