



SAB 22 HT2-65 G1/4-AG


Suction cup SAB HT2, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.

Technical data

Attribute	Value
Suction cup material	High temperature material HT2
Material hardness [Shore A]	65.0 Shore A
Size	22.00
Temperature resistance	200.0 °C
Number of folds	1.5
Connection	G1/4-AG
Nipple material	Aluminum

Design data

Attribute	Value
Height H	25.00 mm
Outside diameter D1	22.0 mm
Nominal diameter dn	3.50 mm
Thread G1	G1/4"-M
Thread length LG1	10.0 mm
Key width SW1	16.0 mm
Spring stroke Z	5.8 mm
Diameter Ds	20.6 mm
Diameter Dmax(S)	24.0 mm



Design data SAB 22 HT2-65 G1/4-AG

Art.-Nr.: 10.01.06.02420

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT2
Material hardness [Shore A]	65.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	20.0 mm
Pull-off force	24.00 N
Suction force (-600mbar)	16.00 N
Weight	15.7 g
Lateral force	17.0 N
Volume	1.500 cm ³
Size	22.00
Number of folds	1.5
Connection	G1/4"-M
Product family	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02420

