


FG 52 HT1-60 N018

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	52,00
Körük Sayısı	2,5



Tasarım verileri FG 52 HT1-60 N018

Tasarım verileri

Attribute	Value
Yükseklik H2	13,00 mm
Yükseklik H	48,70 mm
Dış çap D1	52,0 mm
Kafa çapı Dk	18,0 mm
d2	24,6 mm
İç çap d	8,00 mm
Yay stroku Z	25,0 mm
Çap Ds	52,5 mm
Çap Dmax(S)	55,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.02365



Teknik veriler

Attribute	Value
Meme ucu ailesi	N 018
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
İş parçası yarıçapı dak (dışbükey)	35,0 mm
Çekme kuvveti	96,00 N
Emme kuvveti (-600mbar)	28,52 N
Ağırlık	24,40 g
Cilt	37,587 cm ³
Boyut	52,00
Körük Sayısı	2,5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02365



WWW.SCHMALZ.COM/10.01.06.02365