




Технические данные

Attribute	Value
Материал присоски	Высокотемпературный материал HT2
Твердость материала [Shore A]	65,0 Shore A
Размеры (ДхШ)	80 x 40
Соединение	G3/8-IG
Материал ниппеля	никелированный

SAOB 80x40 HT2-65 G3/8-IG

Присоска SAOB HT2, доступная в различных размерах, поставляется с соединительным ниппелем, вулканизированным в эластомерную часть.



Конструктивные данные

Attribute	Value
Длина L1	73,30 mm
Ширина B1	40,00 mm
Высота H	37,70 mm
Номинальный диаметр dn	6,00 mm
Резьба G1	G3/8"-F
Длина резьбы LG1	9,0 mm
Размер гаечного ключа SW1	22,0 mm
Ход пружины Z	9,0 mm
Ширина присоски Bs	40,60 mm
Ls	80,60 mm

Конструктивные данные SAOB 80x40 HT2-65 G3/8-IG

Art.-Nr.: 10.01.06.02445



Технические данные

Attribute	Value
Материал присоски	Высокотемпературный материал HT2
Твердость материала [Shore A]	65,0 Shore A
Внутренний диаметр шланга (реком.) d	6,0 mm
Радиус заготовки мин. (выпуклый)	40,0 mm
Сила отрыва	100,00 N
Всасывающая сила (-600 мбар)	65,00 N
Вес	79,4 g
Размеры (ДхШ)	80 x 40
Поперечная сила	98,0 N
Объем	21,800 cm ³
Количество складок	1,5
Семейство продуктов	SAOB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02445

