




SAB 22 HT2-65 G3/8-IG

Çeşitli çaplarda mevcut olan vantuz SAB HT2, elastomer parçaya vulkanize edilmiş bağlantı nipeli ile birlikte teslim edilir.



Tasarım verileri SAB 22 HT2-65 G3/8-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65.0 Shore A
Boyut	22.00
Sıcaklık direnci	200.0 °C
Körük Sayısı	1.5
Bağlantı	G3/8-IG
Meme ucu malzemesi	Nikel kaplama

Tasarım verileri

Attribute	Value
Yükseklik H	41.00 mm
Dış çap D1	22.0 mm
Nominal çap dn	3.50 mm
Dış G1	G3/8"-F
Dış uzunluğu LG1	9.5 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	5.8 mm
Çap Ds	20.6 mm
Çap Dmax(S)	24.0 mm

Art.-Nr.: 10.01.06.02421

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65.0 Shore A
Hortum çapı (tavsiye edilen) d	4.0 mm
İş parçası yarıçapı dak (dışbükey)	20.0 mm
Çekme kuvveti	24.00 N
Emme kuvveti (-600mbar)	16.00 N
Ağırlık	42.8 g
Yanal kuvvet	17.0 N
Cilt	1.500 cm ³
Boyut	22.00
Körük Sayısı	1.5
Bağlantı	G3/8"-F
Ürün ailesi	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02421

WWW.SCHMALZ.COM/10.01.06.02421