


Art.-Nr.: 10.01.06.02425



SAB 30 HT2-65 G3/8-IG

Suction cup SAB HT2, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.



Design data SAB 30 HT2-65 G3/8-IG

Technical data

Attribute	Value
Suction cup material	High temperature material HT2
Material hardness [Shore A]	65.0 Shore A
Size	30.00
Temperature resistance	200.0 °C
Number of folds	1.5
Connection	G3/8-IG
Nipple material	Nickel plated

Design data

Attribute	Value
Height H	44.00 mm
Outside diameter D1	32.0 mm
Nominal diameter dn	4.00 mm
Thread G1	G3/8"-F
Thread length LG1	9.5 mm
Key width SW1	22.0 mm
Spring stroke Z	9.0 mm
Diameter Ds	30.6 mm
Diameter Dmax(S)	34.0 mm



Art.-Nr.: 10.01.06.02425

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT2
Material hardness [Shore A]	65.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	40.0 mm
Pull-off force	33.00 N
Suction force (-600mbar)	22.00 N
Weight	48.5 g
Lateral force	29.0 N
Volume	5.600 cm ³
Size	30.00
Number of folds	1.5
Connection	G3/8"-F
Product family	SAB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02425

