




FGA 63 HT1-60 N018

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	63.00
Number of folds	1.5



Design data

Attribute	Value
Height H_2	13.00 mm
Height H	34.00 mm
Outside diameter D_1	67.0 mm
Head diameter D_k	18.0 mm
Internal diameter d_1	14.5 mm
d_2	44.5 mm
Internal diameter d	8.00 mm
Spring stroke Z	15.0 mm
Diameter D_s	60.0 mm
Height H_3	18.80 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FGA 63 HT1-60 N018

Art.-Nr.: 10.01.06.02473

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT1
Workpiece radius min. (convex)	75.0 mm
Suction force (-600mbar)	85.00 N
Weight	23.80 g
Size	63.00
Number of folds	1.5
Product family	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02473

**Ordering Data Accessories 10.01.06.02473**

Typ		Item number
Suction cup connection nipple	SA-NIP N018 G1/4-AG DN440	10.01.06.01065
Suction cup connection nipple	SA-NIP N018 G1/4-IG DN440	10.01.06.01066

