

FGA 78 HT1-60 N019


Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	78,00
Körük Sayısı	1,5

Tasarım verileri

Attribute	Value
Yükseklik H2	19,70 mm
Yükseklik H	47,00 mm
Dış çap D1	83,0 mm
Kafa çapı Dk	24,7 mm
İç çap d1	21,8 mm
d2	54,0 mm
İç çap d	11,80 mm
Yay stroku Z	16,0 mm
Çap Ds	74,0 mm
Yükseklik H3	31,40 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri FGA 78 HT1-60 N019

Körüklü vantuz (yuvarlak)

FGA 78 HT1-60 N019



Art.-Nr.: 10.01.06.02474



Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
İş parçası yarıçapı dak (dışbükey)	70,0 mm
Emme kuvveti (-600mbar)	137,40 N
Ağırlık	55,60 g
Boyut	78,00
Körük Sayısı	1,5
Ürün ailesi	FGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02474



Sipariş Verisi Aksesuarlar 10.01.06.02474

Typ	Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N019 G1/4-AG DN820
Vantuz bağlantı nipeli	SA-NIP N019 G1/4-IG DN820



WWW.SCHMALZ.COM/10.01.06.02474