


FG 62 HT1-60 N018

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	62.00
Körük Sayısı	2.5



Tasarım verileri FG 62 HT1-60 N018

Tasarım verileri

Attribute	Value
Yükseklik H2	13.00 mm
Yükseklik H	54.00 mm
Dış çap D1	62.0 mm
Kafa çapı Dk	18.0 mm
d2	29.5 mm
İç çap d	8.00 mm
Yay stroku Z	29.0 mm
Çap Ds	62.2 mm
Çap Dmax(S)	65.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.06.02475

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 018
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
İş parçası yarıçapı dak (dışbükey)	42.0 mm
Çekme kuvveti	137.00 N
Emme kuvveti (-600mbar)	41.01 N
Ağırlık	39.2 g
Cilt	61.122 cm ³
Boyut	62.00
Körük Sayısı	2.5
Ürün ailesi	FG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02475

WWW.SCHMALZ.COM/10.01.06.02475