




FGAO 18x14 SI-HD-65 N016

Технические данные

Attribute	Value
Материал присоски	силикон SI-HD
Твердость материала [Shore A]	65,0 Shore A
Размеры (ДхШ)	18 x 14
Количество складок	1,5



Конструктивные данные FGAO 18x14 SI-HD-65 N016

Конструктивные данные

Attribute	Value
Длина L1	18,20 mm
Ширина B1	13,70 mm
Высота H	13,50 mm
Внутренний диаметр d	4,50 mm
Ход пружины Z	5,0 mm
Ширина присоски Bs	12,50 mm
Ls	16,90 mm
Lмакс.(S)	18,50 mm
Bмакс(S)	14,00 mm
Длина L2	9,50 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Art.-Nr.: 10.01.06.02458



Технические данные

Attribute	Value
Материал присоски	силикон SI-HD
Твердость материала [Shore A]	65,0 Shore A
Радиус заготовки мин. (выпуклый)	6,0 mm
Всасывающая сила (-600 мбар)	2,10 N
Вес	1,2 g
Размеры (ДхШ)	18 x 14
Количество складок	1,5
Семейство продуктов	FGAO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02458

